



Ordering part no.: 900040000G


QIG Part no.: 625039500G

CMA-E01 User Guide

Rev. 1.0

Beam angle selectors

(Only available for motorized illuminators, e.g., CM48i8a-1040) These buttons provide quadruple proportions of adjustable angles from the narrowest, 33%, 66%, to the widest. These angles vary with different models. When a beam angle is selected, you can use the fine-tune buttons below to tune for a desired effect.



After a preset beam angle is selected, use these buttons to fine-tune. T stands for tele, W for wide.

This page is intentionally left blank.